



Mini Cosmetic Fridge

with LED light mirror




USER GUIDE




CONNECTORS

**AC CONECTION CABLE
(HOUSEHOLD)**



OPERATING PANEL



CAPACITY	4 L / 6 cans
ITEM DIMENSIONS	10" x 7" x 10.5"
ITEM WEIGHT (LBS)	1.59 kg
POWER	22W (9V DC in)
TEMPERATURE RANGE	50-59 Degrees °F



IMPORTANT SAFEGUARDS

HOUSE HOLD POWER (AC 110-240V)

1. Make sure the switch on the back of the cooler is in the OFF position.

2. Plug the AC power adapter into the DC socket at the back of the cooler.

3. Connect the AC adapter to an AC wall outlet

4. Slide the power switch to the ON position. The green light will go on and the COOLING begins.

LED mirror built-in with touch control switch, press the switch once to turn on the light for low brightness, press the switch three times for strong light, press the switch four times to turn off the light, this is a loop control program.



WARNING AND NOTICE

Please read below before using your mini cooler.

1. To prevent the fan from stopping, the unit over-heating then causing fire, please do not cover the fan with any kind of cloth, towel, etc.

2. Make sure the power cords are firmly attached to the unit and snugly plugged into the outlet(s).

3. Keep the mini cooler away from flammable items and moisture to prevent possible over-heating, fires and/or explosions.

4. Do not take the cooler apart or attempt to reconfigure it.

5. Do not rinse with water - use a damp cloth.





01/

- To power your mini fridge with AC power, connect the AC power cord into the back of the unit and a standard power outlet.

02/

- It is important to understand there is no thermostat, and the maximum chill temperature will not reach below 50° F. It is the ideal temperature for beauty products and beverages, but not recommended for perishable foods or prolonged storage of dairy products.